This document was generated on 10/11/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1300478009

Status: Active

Overview: Brad Industrial Ethernet Solutions

Description: Brad RJ-45 Field Attachable Connector, 8 Poles, Right-Angle, Male, Shielded, IDC Termination, AWG 24-22



Series image - Reference only

Documents:

Drawing (PDF)
Datasheet (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E361772
General	
Product Family	Field Attachable / Accessories
Series	130047
Approvals	cCSAus certified
Comments	POE+ according to IEEE 802.3AT
Communication Speed	10-Gigabit Ethernet
IP Rating	IP20
Material - Contact	Brass
Overview	Brad Industrial Ethernet Solutions
Product Name	RJ45 Cat6A
Taxonomy	Circular Industrial Connectors
Type	Field Attachable Connector
UPC	889056622820
Physical	
Cable Diameter	5.50-10.00mm (.216-.393")
Coupling Type	Push to Lock
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	X-coded
Material - Connector Body	Zinc Die-Cast with Nickel
Material - Coupling Nut	Clear UL 94 V0
Material - Plating Mating	Gold
Net Weight	22.582/g
Orientation	90° Angle
Poles	8
Temperature Range - Operating	-40°C to +85°C
Wire Size AWG	24-22/1
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	48V
Material Info	
Engineering Number	E6AS07-5
Reference - Drawing Numbers	
Sales Drawing	1300478009-000

EU ELV
Not Relevant

EU RoHS
Compliant

China RoHS

REACH SVHC
Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_UKCA - Declaration of Conformity	CER_4000410293_00_000.pdf

Search Parts in this Series
130047 Series

This document was generated on 10/11/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION