

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300480104

Status:

Active

Overview:

Brad Industrial Ethernet Solutions

Description:

Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (Straight) to Male (Straight), 24 AWG, Teal TPE Cable, 10.0m (32.81') Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E200650
General	
Product Family	Industrial Cordsets
Series	130048
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Industrial Ethernet Solutions
Performance Category	5e
Product Name	Micro-Change (M12)
Region	America, Asia, Europe
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	78678806029
Physical	
Cable Diameter	6.10mm (.240")
Cable Length	10.0m (32.81')
Color - Cable Jacket	Teal
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	0.430/kg
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +75°C
Wire Size AWG	24
Wire/Cable Type	Unshielded TPE/AWM 2463
Electrical	
Current - Maximum per Contact	1.5A
Voltage - Maximum	125V
Material Info	
Engineering Number	E11A06004M100
Reference - Drawing Numbers	
Sales Drawing	1300480095-00P, SD-130048-001-001



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2022)4187-DC (10 June 2022)	
Lead	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained
ZZCERT_CE - Declaration of Conformity	CER_4000408918_00_000.pdf
ZZCERT_UKCA - Declaration of Conformity	CER_4000410292_00_000.pdf

Search Parts in this Series

130048 Series

This document was generated on 10/18/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION