

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300640459](#)
Status: **Active**
Overview: BradPower Cordsets and Receptacles
Description: BradPower D-Size (1 3/8"–M35) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 10 AWG, Black TPE Cable, 12.0m (39.37') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Industrial Cordsets
 Series [130064](#)
 Connector End A BradPower D-Size (1 3/8"–M35)
 Connector End B BradPower D-Size (1 3/8"–M35)
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [BradPower Cordsets and Receptacles](#)
 Product Name BradPower D-Size
 Taxonomy Circular Industrial Cordsets
 Type Double Ended
 UPC 78172546618

Physical

Cable Diameter 13.46mm (.530")
 Cable Length 12.0m (39.37")
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Female-Male
 Keyway Single
 LED Indicator No
 Material - Cable Jacket TPE
 Material - Connector Body TPE
 Material - Coupling Nut Anodized Aluminum
 Material - Plating Mating Gold
 Net Weight 366.000/g
 Orientation Straight to Straight
 Poles 4
 Temperature Range - Operating -20° to +90°C
 Wire Size AWG 10
 Wire/Cable Type TC-ER

Electrical

Current - Maximum per Contact 32.0A
 Voltage - Maximum 600V AC/DC

Material Info

Engineering Number CC4030K17M120G

Reference - Drawing Numbers

Sales Drawing SD-130064-006-001



Series image - Reference only

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2022)4187-DC (10 June 2022)
 Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

China RoHS

Not Relevant

Compliant with

Exemption 3

Not Contained

CER_4000410036_00_000.pdf

CER_4000410293_00_000.pdf

Search Parts in this Series

[130064 Series](#)