

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300640463](#)
Status: **Active**
Overview: [BradPower Cordsets and Receptacles](#)
Description: BradPower D-Size (1 3/8"–M35) Double-Ended Cordset, 4 Poles, Male (Straight) to Female (Straight), 10 AWG, Black TPE Cable, 30.0m (98.40') Length



Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E258922
General	
Product Family	Industrial Cordsets
Series	130064
Connector End A	BradPower D-Size (1 3/8"–M35)
Connector End B	BradPower D-Size (1 3/8"–M35)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	BradPower Cordsets and Receptacles
Product Name	BradPower D-Size
Taxonomy	Circular Industrial Cordsets
Type	Double Ended
UPC	78172546622
Physical	
Cable Diameter	13.46mm (.530")
Cable Length	30.0m (98.40')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	TPE
Material - Connector Body	TPE
Material - Coupling Nut	Anodized Aluminum
Material - Plating Mating	Gold
Net Weight	31222.000/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20° to +90°C
Wire Size AWG	10
Wire/Cable Type	TC-ER
Electrical	
Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC
Material Info	
Engineering Number	CC4030K17M300G
Reference - Drawing Numbers	
Sales Drawing	SD-130064-006-001

EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per -
D(2022)4187-DC (10
June 2022)
Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

China RoHS

Not Relevant

Compliant with
Exemption 3

RoHS Phthalates

ZZCERT_CE -

Declaration of

Conformity

ZZCERT_UKCA

- Declaration of

Conformity

Not Contained

CER_4000383479_00_000.pdf

CER_4000410542_00_000.pdf

Search Parts in this Series

[130064](#) Series