

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130083-0233](#)
Status: **Active**
Description: Woodhead® POW-R-MITE® Industrial Duty Cable Reel, 10/3 SOW, 12.19m (40.0')
 Cord Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E22769

General

Product Family	Electric Reels
Series	130083
Cable Length	N/A
Comments	Applications: Vertical Lift, Drag, Recovery and Horizontal Stretch with 10% Sag.
Depth	0.34m (13.50")
Duty	Industrial
Enclosure Rating	NEMA 4
Height	0.37m (14.50")
NEMA Configuration	N/A
Product Name	POW-R-MITE®
Type	Cable Reel
UPC	78678879243
Width	244.35mm (9.620")
Woodhead	Yes

Physical

Cable Movement	Ratchet Lock
Cord Length	12.19m (40.0')
Drum Lock	Ratchet
Guide Arm	5° increments over 270° Arc
Material - Coating	Powder Coating
Material - Housing	Cast Aluminum
Mounting Style	Rigid
Number of Conductors	3
Packaging Type	Carton
Primary Cord/Cable Entry	1" NPT
Retraction Weight	1.8kg (4.0 lb)
Wire Size AWG	10

Electrical

Bulb Included	N/A
Cord Type	10/3 SOW
Current - Maximum per Contact	22A
GFCI	No
Lamp Type	N/A
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage - Maximum	600V

Material Info

Old Part Number 92434

EU RoHS

Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130083Series](#)

This document was generated on 08/24/2012

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION