

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300910085](#)  
**Status:** **Active**  
**Overview:** [Reels - Woodhead](#)  
**Description:** Woodhead Standard Duty Reel with Flying Leads, 12/3 SJTOW Cord, 10.67m (35.0') Cord Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Datasheet \(PDF\)](#)

**Agency Certification**

CSA LR29921  
 UL E22769

**General**

Product Family Electric Reels  
 Series [130091](#)  
 Cable Length 0.457m (1.50')  
 Depth 0.30m (11.75")  
 Duty Standard  
 Enclosure Rating NEMA 1  
 Height 0.36m (14.25")  
 NEMA Configuration NEMA 5-15  
 Overview [Reels - Woodhead](#)  
 Product Name Super-Safeway  
 Taxonomy Electric Reels  
 Type Cord Reel  
 UPC 78678833608  
 Width 196.85mm (7.750")

**Physical**

Cable Movement Ratchet Lock  
 Cord Length 10.67m (35.0')  
 Drum Lock Ratchet  
 Guide Arm 2 - Position  
 Material - Coating Powder Coating  
 Material - Housing Steel/Polycarbonate  
 Mounting Style Rigid  
 Net Weight 11793.392/g  
 Number of Conductors 3  
 Packaging Type Carton  
 Primary Cord/Cable Entry N/A  
 Retraction Weight 1.4kg (3.0 lb)  
 Wire Size AWG 12

**Electrical**

Bulb Included N/A  
 Cord Type 12/3 SJTOW  
 Current - Maximum per Contact 15.0A  
 GFCI No  
 Lamp Type N/A  
 Lamp Wattage - Maximum N/A  
 On/Off Switch N/A  
 Voltage - Maximum 120V

**Material Info**

Engineering Number 997



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

**Search Parts in this Series**

[130091 Series](#)

Reference - Drawing Numbers  
Sales Drawing

SD-130091-008-001

This document was generated on 08/27/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**