

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300950124

Status:

Active

Overview:

Pulling Grips

Description:

Heavy Duty Wire Mesh Pulling Grip, Double Weave, Rotating Eye, Standard Mesh Length 0.406m (16.00"), Approximate Break Strength 2510.12kg (5600 lbs)



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
CSA	LR32159
General	
Product Family	Cable Grips
Series	130095
Eye Type	Rotating
O-Ring	N/A
Overview	Pulling Grips
Product Name	Heavy Duty
Taxonomy	Cable Grips
Type	Pulling Grip
UPC	78678835865
Physical	
Approximate Break Strength	2510.12kg (5600 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	12.70-15.49mm (.500-.610")
Color - Grommet	N/A
Eye Diameter	7/8"
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.406m (16.00")
Number of Holes	N/A
Thread Size	N/A
Material Info	
Engineering Number	35865
Reference - Drawing Numbers	
Sales Drawing	SD-130095-107-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Relevant	
REACH SVHC	
Not Relevant	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Relevant

Search Parts in this Series

130095 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION