

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1300950179

Status:

Active

Overview:

Pulling Grips

Description:

Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Short Mesh Length 0.61m (24.00"), Cable Range 76.20-88.66mm (3.000-3.492"), Approximate Break Strength 11113.01kg (24500 lbs)



Documents:

[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)

Agency Certification	
CSA	LR32159
General	
Product Family	Cable Grips
Series	130095
Comments	Cable Eye Thickness 1/2"
Eye Type	Flexible
O-Ring	N/A
Overview	Pulling Grips
Product Name	Medium Duty
Taxonomy	Cable Grips
Type	Pulling Grip
UPC	78678835947
Physical	
Approximate Break Strength	11113.01kg (24500 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	76.20-88.65mm (3.000-3.490")
Color - Grommet	N/A
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.61m (24.00")
Number of Holes	N/A
Thread Size	N/A
Material Info	
Engineering Number	35947
Reference - Drawing Numbers	
Sales Drawing	SD-130095-103-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130095 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION