

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300970262](#)
Status: **Active**
Overview: [strainrelief_cord_grips](#)
Description: Dust-Tight Strain Relief Wide Range Grip, 3/4" NPT, Straight Male, Cable Diameter 13.21-18.54mm, Approximate Break Strength 204.12kg

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR32159

General

Product Family	Cable Grips
Series	130097
Eye Type	N/A
Insulated	No
O-Ring	No
Overview	strainrelief_cord_grips
Product Name	Dust-Tight
Type	Strain Relief Grip
Woodhead	Yes

Physical

Approximate Break Strength	204.12kg
Bale Length	N/A
Body Style	Straight
Cable Diameter	13.21-18.54mm
Color - Grommet	N/A
Gender	Male
Material - Body	Zinc Plated Steel
Material - Grip	Galvanized Steel
Mesh Length	0.19m
Number of Holes	N/A
Strain Relief Force	35 lbs
Thread Size	3/4" NPT

Material Info

Old Part Number 36508

Reference - Drawing Numbers

Sales Drawing SD-130097-002



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
130097Series