

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300990167](#)
Status: **Active**
Overview: [Strain-Relief Cord Grips](#)
Description: MAX-LOC/Watertite Cord Grips, 1/2" NPT, Straight Male, Body Size F2, Cable Diameter 9.53-11.10mm (.375-.437")

Documents:

[Drawing \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Grips
Series	130099
Eye Type	N/A
NEMA Rating	NEMA 3R
O-Ring	N/A
Overview	Strain-Relief Cord Grips
Product Name	MAX-LOC, Watertite
Taxonomy	Cable Grips
Type	Strain Relief Grip
UPC	78678822650
Use With	1/2" NPT MAX-LOC Lock Nut 1300990143 , MAX-LOC O-Ring, 1/2" NPT 1301800314 , 1/2" NPT MAX-LOC Gasket 1300990149

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	9.53-11.10mm (.375-.437")
Color - Grommet	Green
Gender	Male
Material - Body	Nylon
Material - Grip	Stainless Steel
Mesh Length	N/A
Net Weight	210.000/g
Number of Holes	1
Thread Size	1/2" NPT

Material Info

Engineering Number 5631M

Reference - Drawing Numbers

Sales Drawing SD-130099-007-001



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[130099 Series](#)