

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130102-0086](#)  
**Status:** **Active**  
**Description:** Super-Safeway™ Rubber Hand Lamp Only with 100W Quick Open Guard and Reflector with Side Outlet

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family	Portable Lighting
Series	<a href="#">130102</a>
Depth	101.60mm
Height	374.65mm
Length	N/A
NEMA Configuration	N/A
Outlet	Side
Product Name	Super-Safeway™
Type	Hand Lamps
Woodhead	Yes

**Physical**

Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Duty	Industrial
Guard Included	No
Guard Type	Metal Wire
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Incandescent
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

**Material Info**

Old Part Number 105U



**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Not Reviewed**  
**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130102Series](#)