

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020087](#)

Status: **Active**

Overview: [Hand Lamps](#)

Description: Super-Safeway Rubber Hand Lamp with 100W, Quick Open Guard with Reflector, with Side Outlet, Cord Length 7.62m (25.0'), Cord Type 16/3 SOOW

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Portable Lighting
Series	130102
NEMA Configuration	NEMA 5-15
Outlet	Side
Overview	Hand Lamps
Product Name	Super-Safeway
Taxonomy	Lamps and Lights
Type	Hand Lamps
UPC	78678879409

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Depth	101.60mm (4.000")
Duty	Industrial
Guard Included	Yes
Guard Type	Quick Open, Reflector
Height	374.65mm (14.750")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	240V

Material Info

Engineering Number	105UA163
--------------------	----------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130102 Series](#)