

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020158](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway Rubber Hand Lamp with 300W, Open End Guard, with Receptacle

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374
 UL E59251

General

Product Family Portable Lighting
 Series [130102](#)
 NEMA Configuration N/A
 Outlet Side
 Overview [Hand Lamps](#)
 Product Name Super-Safeway
 Taxonomy Lamps and Lights
 Type Hand Lamps
 UPC 78678860540

Physical

Cord Length - Primary N/A
 Cord Length - Secondary N/A
 Depth 190.50mm (7.500")
 Duty Industrial
 Guard Included Yes
 Guard Type Open End
 Height 371.35mm (14.620")
 Length N/A
 Material - Guard #8 Gauge Zinc-plated Steel
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Lamp Type A23
 Lamp Wattage - Maximum 300W
 Lumens 1000
 On/Off Switch No
 Voltage (Fixture) - Maximum 240V

Material Info

Engineering Number 111U



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130102 Series](#)