

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020192](#)
Status: **Active**
Description: Super-Safeway™ Rubber Hand Lamp with 300W Open End Reflector Guard with Receptacle

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family	Portable Lighting
Series	130102
Depth	190.50mm
Height	371.35mm
Length	N/A
NEMA Configuration	N/A
Outlet	Side
Product Name	Super-Safeway™
Type	Hand Lamps
Woodhead	Yes
Physical	
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Duty	Industrial
Guard Type	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Electrical	
Bulb Type	Incandescent
Lamp Type	A23
Lamp Wattage - Maximum	300W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Material Info

Old Part Number 115U



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130102Series](#)