

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301020200

Status:

Active

Overview:

Hand Lamps

Description:

Super-Safeway Rubber Hand Lamp with 300W, Open End Guard with Reflector, with Switch and Receptacle, 15.24m (50.0') 16/3 SOOW



Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Portable Lighting
Series	130102
NEMA Configuration	NEMA 5-15
Outlet	Side
Overview	Hand Lamps
Product Name	Super-Safeway
Taxonomy	Lamps and Lights
Type	Hand Lamps
UPC	78678879446
Physical	
Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	190.50mm (7.500")
Duty	Industrial
Guard Included	Yes
Guard Type	Open End, Reflector
Height	371.35mm (14.620")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A23
Lamp Wattage - Maximum	300W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V
Material Info	
Engineering Number	115USB163

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130102 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION