

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130102-0211](#)
Status: **Active**
Description: Super-Safeway™ Rubber Hand Lamp with Switch & Receptacle

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family	Portable Lighting
Series	130102
Depth	80.01mm (3.150")
Height	174.63mm (6.875")
Length	N/A
NEMA Configuration	N/A
Outlet	Side
Product Name	Super-Safeway™
Type	Hand Lamps
UPC	78678860896
Woodhead	Yes

Physical

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Duty	Industrial
Guard Included	No
Guard Type	N/A
Material - Guard	N/A
Mounting Style	Hand Held
Net Weight	412.760/g
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	240V

Material Info

Old Part Number 1175US



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series
[130102Series](#)