

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301020222](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway Rubber Hand Lamp, Nylon Quick Open Guard, with Switch and Receptacle

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374
 UL E59251

General

Product Family Portable Lighting
 Series [130102](#)
 NEMA Configuration N/A
 Outlet Side
 Overview [Hand Lamps](#)
 Product Name Super-Safeway
 Taxonomy Lamps and Lights
 Type Hand Lamps
 UPC 78678860589

Physical

Cord Length - Primary N/A
 Cord Length - Secondary N/A
 Depth 127.00mm (5.000")
 Duty Industrial
 Guard Included Yes
 Guard Type Quick Open
 Height 400.05mm (15.750")
 Length N/A
 Material - Guard Nylon
 Mounting Style Hand Held
 Net Weight 560.639g
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Cord Type - Primary 16/3 SOOW
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 240V

Material Info

Engineering Number 118US



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130102 Series](#)