

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301020259](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Safeway Phenolic Hand Lamp Only with 100W, Screw Release Guard with Reflector, with Switch and Side Outlet

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
 Series [130102](#)  
 NEMA Configuration N/A  
 Outlet Side  
 Overview [Hand Lamps](#)  
 Product Name Safety Yellow  
 Taxonomy Lamps and Lights  
 Type Hand Lamps  
 UPC 78678860133

**Physical**

Cord Length - Primary N/A  
 Cord Length - Secondary N/A  
 Depth 101.60mm (4.000")  
 Duty Commercial  
 Guard Included Yes  
 Guard Type Reflector, Screw Release  
 Height 381.00mm (15.000")  
 Length N/A  
 Material - Guard #8 Gauge Zinc-plated Steel  
 Mounting Style Hand Held  
 Net Weight 681.748/g  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
 Lamp Type A21  
 Lamp Wattage - Maximum 100W  
 Lumens 1000  
 On/Off Switch Yes  
 Voltage (Fixture) - Maximum 240V

**Material Info**

Engineering Number 271US



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130102 Series](#)