

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130102-0272](#)  
**Status:** **Active**  
**Description:** Safeway® Phenolic Hand Lamp with 100W Screw Release Guard Switch Outlet

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
 Series [130102](#)  
 NEMA Configuration N/A  
 Outlet Side  
 Product Name Safety Yellow®  
 Type Hand Lamps  
 Woodhead Yes

**Physical**

Cord Length - Primary N/A  
 Cord Length - Secondary N/A  
 Depth 101.60mm  
 Duty Commercial  
 Guard Included No  
 Guard Type Metal Wire  
 Height 381.00mm  
 Length N/A  
 Material - Guard #8 Gauge Zinc-plated Steel  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
 Lamp Type A21  
 Lamp Wattage - Maximum 100W  
 Lumens 1000  
 On/Off Switch Yes  
 Voltage (Fixture) - Maximum 240V

**Material Info**

Old Part Number 276US



*image - Reference only*

**EU RoHS**

**ELV and RoHS  
 Compliant  
 REACH SVHC  
 Not Reviewed  
 Low-Halogen Status  
 Not Reviewed**

**China RoHS**



**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[130102Series](#)