

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301040038](#)  
**Status:** **Active**  
**Overview:** [Specialty Lighting](#)  
**Description:** Haztex Incandescent Hazardous and Wet Location Hand Lamp Low Voltage for Use With Low Voltage Workstation, 75W with 12V Lamp, 14/3 SOOW Secondary Cord Type, Cord Length 15.24m (50.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR39801

**General**

Product Family Portable Lighting  
 Series [130104](#)  
 Comments Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)  
 NEMA Configuration Non-NEMA  
 NEMA Rating NEMA 4X  
 Outlet None  
 Overview [Specialty Lighting](#)  
 Product Name Haztex  
 Taxonomy Lamps and Lights  
 Type Hand Lamps, Specialty Light  
 UPC 78678800722

**Physical**

Cord Length - Primary 15.24m (50.0')  
 Cord Length - Secondary N/A  
 Depth 127.00mm (5.000")  
 Duty Hazardous, Wet Location  
 Guard Included Yes  
 Guard Type Cast Aluminum  
 Height 419.10mm (16.500")  
 Length N/A  
 Material - Globe Tempered Soda-Lime Glass  
 Material - Guard Cast Aluminum  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Incandescent  
 Cord Type - Secondary 14/3 SOOW  
 Lamp Type A21  
 Lamp Wattage - Maximum 100W  
 Lumens 1000  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 12V AC/DC

**Material Info**

Engineering Number 1645-12



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130104 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**