

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301040042](#)
Status: **Active**
Overview: Specialty Lighting
Description: Haztex Incandescent Hazardous and Wet Location Hand Lamp, 100W, 14/3 SOOW Cord Type, 7.62m (25.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR39801
 UL E30252

General

Product Family Portable Lighting
 Series [130104](#)
 Comments Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
 NEMA Configuration NEMA 5-15
 NEMA Rating NEMA 4X
 Outlet None
 Overview [Specialty Lighting](#)
 Product Name Haztex
 Taxonomy Lamps and Lights
 Type Hand Lamps, Specialty Light
 UPC 78678861433

Physical

Cord Length - Primary 7.62m (25.0')
 Cord Length - Secondary N/A
 Depth 127.00mm (5.000")
 Duty Hazardous, Wet Location
 Guard Included Yes
 Guard Type Cast Aluminum
 Height 419.10mm (16.500")
 Length N/A
 Material - Globe Tempered Soda-Lime Glass
 Material - Guard Cast Aluminum
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Incandescent
 Cord Type - Primary 14/3 SOOW
 Lamp Type A21
 Lamp Wattage - Maximum 100W
 Lumens 1000
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 61430A143



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130104 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION