

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301040044](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Haztex Incandescent Hazardous and Wet Location Hand Lamp, 100W, 14/3 SOOW Cord Type, 15.24m (50.0') Cord Length

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR39801
UL E30252

General

Product Family Portable Lighting
Series [130104](#)
Comments Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Specialty Lighting](#)
Product Name Haztex
Taxonomy Lamps and Lights
Type Hand Lamps, Specialty Light
UPC 78678861434

Physical

Cord Length - Primary 15.24m (50.0')
Cord Length - Secondary N/A
Depth 127.00mm (5.000")
Duty Hazardous, Wet Location
Guard Included Yes
Guard Type Cast Aluminum
Height 419.10mm (16.500")
Length N/A
Material - Globe Tempered Soda-Lime Glass
Material - Guard Cast Aluminum
Mounting Style Hand Held
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 14/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 61430B143



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130104](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION