

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301040049](#)
Status: **Active**
Overview: [Specialty Lighting](#)
Description: Haztex Incandescent Hazardous and Wet Location Hand Lamp, 100W, 16/3 SOOW Cord Type, 30.48m (100.0') Cord Length



Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
CSA	LR39801
UL	E30252
General	
Product Family	Portable Lighting
Series	130104
Comments	Class I, Division 1, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone 1, Group IIB (UL)
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Overview	Specialty Lighting
Product Name	Haztex
Taxonomy	Lamps and Lights
Type	Hand Lamps, Specialty Light
UPC	78678861439
Physical	
Cord Length - Primary	30.48m (100.0')
Cord Length - Secondary	N/A
Depth	127.00mm (5.000")
Duty	Hazardous, Wet Location
Guard Included	Yes
Guard Type	Cast Aluminum
Height	419.10mm (16.500")
Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Engineering Number	61430D163

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130104](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION