

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130105-0045](#)  
**Status:** **Active**  
**Description:** Haztex® Incandescent Hazardous and Wet Location Hand Lamp with LOVOLT® In-line Transformer 100W, 16/3 SOOW Primary Cord Type, Cord Length 7.62m (25.0' )

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family	Portable Lighting
Series	<a href="#">130105</a>
Comments	Class I, Division I, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone I, Group IIB (UL)
Depth	127.00mm (5.000")
Height	419.10mm (16.500")
Length	N/A
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Product Name	Haztex®
Type	Specialty Light
Woodhead	Yes

**Physical**

Cord Length - Primary	3.04m (10.0' )
Cord Length - Secondary	7.62m (25.0' )
Duty	Hazardous, Wet Location
Guard Included	No
Guard Type	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	75W
Lumens	750
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

**Material Info**

Old Part Number	1635-12A
UPC	78678862505



**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
 Not Reviewed

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130105Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**