

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301060114](#)  
**Status:** **Active**  
**Overview:** [Stringlights](#)  
**Description:** Super-Safeway Molded Rubber Stringlight 200W 12/3 SOOW 1.52m (5.0') Lead 5 Sockets with Guards, NEMA 5-20 Plug, Overall Length 15.24m (50.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
 Series [130106](#)  
 NEMA Configuration NEMA 5-20  
 NEMA Rating Rain Tight  
 Outlet None  
 Overview [Stringlights](#)  
 Product Name Super-Safeway  
 Taxonomy Lamps and Lights  
 Type String Lights  
 UPC 78678879895

**Physical**

Cord Length - Primary 1.52m (5.0')  
 Cord Length - Secondary 1.52m (5.0')  
 Depth 47.625mm (1.875")  
 Duty Industrial  
 Guard Included Yes  
 Guard Type Steel  
 Height 107.95mm (4.250")  
 Length 15.24m (50.0')  
 Material - Guard #8 Gauge Zinc-plated Steel  
 Mounting Style Stringer  
 Packaging Type Carton  
 Socket Construction Rubber Molded

**Electrical**

Bulb Type Incandescent  
 Cord Type - Primary 12/3 SOOW  
 Lamp Type A21  
 Lamp Wattage - Maximum 200W  
 Lumens 2000  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 323525



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130106 Series](#)