

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130108-0126](#)
Status: **Active**
Description: Super-Safeway™ 13W Fluorescent Hand Lamp 230V with Cord Ballast Location and Switch, Cord Type 18/3 SJTOOW, Cord Length 15.24m

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
 Series [130108](#)
 NEMA Configuration N/A
 Outlet None
 Product Name Super-Safeway™
 Type Hand Lamps
 Woodhead Yes

Physical

Cord Length - Primary 15.24m
 Cord Length - Secondary N/A
 Depth 38.10mm
 Duty Industrial
 Guard Included No
 Guard Type N/A
 Height 66.04mm
 Length 342.90mm
 Material - Globe Butyrate
 Material - Guard Nitrile Rubber 80 Shore A
 Mounting Style Hand Held
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Fluorescent
 Cord Type - Primary 18/3 SJTOOW
 Lamp Type PL13/41
 Lamp Wattage - Maximum 13W
 Lumens 900
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 230VAC 50 HZ

Material Info

Old Part Number 1085-3-P
 UPC 78678867082



EU RoHS

Not RoHS Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130108Series](#)