

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130108-0133](#)
Status: **Active**
Description: Super-Safeway™ 13W Fluorescent Hand Lamp Ballast in Handle Handle Only

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374

General

| | |
|--------------------|------------------------|
| Product Family | Portable Lighting |
| Series | 130108 |
| Depth | 38.10mm (1.500") |
| Height | 66.04mm (2.600") |
| Length | 431.80mm (17.000") |
| NEMA Configuration | N/A |
| Outlet | None |
| Product Name | Super-Safeway™ |
| Type | Hand Lamps |
| UPC | 78678885818 |
| Woodhead | Yes |

Physical

| | |
|-------------------------|---------------------------|
| Cord Length - Primary | 7.62m (25.0') |
| Cord Length - Secondary | N/A |
| Duty | Industrial |
| Guard Included | No |
| Guard Type | N/A |
| Material - Globe | Butyrate |
| Material - Guard | Nitrile Rubber 80 Shore A |
| Mounting Style | Hand Held |
| Net Weight | 901.280/g |
| Packaging Type | Carton |
| Socket Construction | N/A |

Electrical

| | |
|-----------------------------|--------------|
| Bulb Type | Fluorescent |
| Cord Type - Primary | 16/3 SOOW |
| Lamp Type | PL13/41 |
| Lamp Wattage - Maximum | 13W |
| Lumens | 900 |
| On/Off Switch | Yes |
| Voltage (Fixture) - Maximum | 120VAC 60 HZ |

Material Info

Old Part Number 1086-3HO



image - Reference only

EU RoHS

Not RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130108Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION