

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130108-0141](#)  
**Status:** **Active**  
**Description:** Super-Safeway™ 27W Fluorescent Machine Light Screw Mount with 18/3 SJTOOW, Overall Cord Length 5.49m (18.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA	LR85374
UL	E174254

**General**

Product Family	Portable Lighting
Series	<a href="#">130108</a>
Depth	76.20mm (3.000")
Height	57.15mm (2.250")
Length	552.45mm (21.750")
NEMA Configuration	NEMA 5-15
Outlet	None
Product Name	Super-Safeway™
Type	Wide Area Lamps
UPC	78678861308
Woodhead	Yes

**Physical**

Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Duty	Industrial
Guard Included	No
Guard Type	N/A
Material - Globe	Clear Polycarbonate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Screw-Bracket
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTOOW
Lamp Type	PL-L 27/41
Lamp Wattage - Maximum	27W
Lumens	2000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

**Material Info**

Old Part Number	1093-3M
-----------------	---------



**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Not Reviewed**  
**Low-Halogen Status  
Not Reviewed**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

130108Series