

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080148](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway 40W Fluorescent Machine Light, Magnet Mount with 18/3 SJTOOW Cord Type, Overall Cord Length 4.57m (15.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR85374
 UL E174254

General

Product Family Portable Lighting
 Series [130108](#)
 NEMA Configuration NEMA 5-15
 Outlet None
 Overview [Wide-Area Lighting Products](#)
 Product Name Super-Safeway
 Taxonomy Lamps and Lights
 Type Wide Area Lamps
 UPC 78678861255

Physical

Cord Length - Primary 4.57m (15.0')
 Cord Length - Secondary N/A
 Depth 76.20mm (3.000")
 Duty Industrial
 Guard Included No
 Guard Type N/A
 Height 57.15mm (2.250")
 Length 798.83mm (31.450")
 Material - Globe Clear Polycarbonate
 Material - Guard Nitrile Rubber 80 Shore A
 Mounting Style Magnetic-Bracket
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type Fluorescent
 Cord Type - Primary 18/3 SJTOOW
 Lamp Type PL-L 40/41
 Lamp Wattage - Maximum 40W
 Lumens 2970
 On/Off Switch Yes
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 1097-3MM



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130108 Series](#)