

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301090028](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Pro-Yellow Nylon 26W Fluorescent Hand Lamp with Switch and Grips Molded, Cord Type 18/3 SJTW, Cord Length 7.62m (25.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E59049

**General**

Product Family Portable Lighting  
 Series [130109](#)  
 NEMA Configuration NEMA 5-15  
 Outlet None  
 Overview [Hand Lamps](#)  
 Product Name Pro-Yellow  
 Type Hand Lamps  
 UPC 78678851149

**Physical**

Cord Length - Primary 7.62m (25.0')  
 Cord Length - Secondary N/A  
 Depth N/A  
 Duty Commercial  
 Guard Included No  
 Guard Type N/A  
 Height N/A  
 Length N/A  
 Material - Guard Polycarbonate  
 Mounting Style Hand Held  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Fluorescent  
 Cord Type - Primary 18/3 SJTW  
 Lamp Type PL-C 26/41/4P  
 Lamp Wattage - Maximum 26W  
 Lumens 1800  
 On/Off Switch Yes  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number WT6F-25



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130109](#) Series