

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301100022](#)  
**Status:** **Active**  
**Overview:** [Wide-Area Lighting Products](#)  
**Description:** Super-Safeway 500W Halogen Floodlight, Magnet Mount, with Guard, Cord Type 16/3 SOOW, Cord Length 7.62m (25.0')

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family Portable Lighting  
 Series [130110](#)  
 NEMA Configuration NEMA 5-15  
 NEMA Rating Rain Tight  
 Outlet None  
 Overview [Wide-Area Lighting Products](#)  
 Product Name Super-Safeway  
 Taxonomy Lamps and Lights  
 Type Wide Area Lamps  
 UPC 78678885061

**Physical**

Cord Length - Primary 7.62m (25.0')  
 Cord Length - Secondary N/A  
 Depth N/A  
 Duty Industrial  
 Guard Included Yes  
 Guard Type Steel  
 Height 374.65mm (14.750")  
 Length 279.40mm (11.000")  
 Material - Globe Tempered Glass  
 Material - Guard #8 Gauge Zinc-plated Steel  
 Mounting Style Magnet  
 Packaging Type Carton  
 Socket Construction N/A

**Electrical**

Bulb Type Quartz Halogen  
 Cord Type - Primary 16/3 SOOW  
 Lamp Type T-3 RSC  
 Lamp Wattage - Maximum 500W  
 Lumens 9200  
 On/Off Switch No  
 Voltage (Fixture) - Maximum 120VAC 60 HZ

**Material Info**

Engineering Number 8506M



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130110 Series](#)