

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301100031](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Wet Location 70W HPS Magnet Mount Area Light, Cord Type 16/3 SJTOW, Cord Length 3.04m (10.0')

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E174254

General

Product Family Portable Lighting
 Series [130110](#)
 NEMA Configuration NEMA 5-15
 NEMA Rating NEMA 3
 Outlet None
 Overview [Wide-Area Lighting Products](#)
 Product Name Woodhead
 Taxonomy Lamps and Lights
 Type Wide Area Lamps
 UPC 78678829247

Physical

Cord Length - Primary 3.04m (10.0')
 Cord Length - Secondary N/A
 Depth 207.26mm (8.160")
 Duty Wet Location
 Guard Included No
 Guard Type N/A
 Height 264.16mm (10.400")
 Length 228.60mm (9.000")
 Material - Globe Clear Polycarbonate
 Material - Guard N/A
 Mounting Style Magnet
 Net Weight 4354.486/g
 Packaging Type Carton
 Socket Construction N/A

Electrical

Bulb Type High Pressure Sodium
 Cord Type - Primary 16/3 SJTOW
 Lamp Type HPS
 Lamp Wattage - Maximum 70W
 Lumens 4300
 On/Off Switch No
 Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 8565



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130110 Series](#)