

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301280139](#)
Status: **Active**
Description: Heavy Duty Stranded Cable, Type SOOW-SOW, 16 AWG, 3 Conductors, 76.20m Length, Yellow

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	130128
Crimp Quality Equipment	Yes
Product Name	Heavy Duty
Taxonomy	Industrial Cable
UPC	78678879956

Physical

Cable Length	76.20m
Circuits (Loaded)	3
Color - Cable Jacket	Yellow
Insulation	EP Rubber
Net Weight	0.039/kg
Outer Jacket Diameter	9.80mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	16
Wire/Cable Type	SOOW, SOW

Electrical

Current - Maximum per Contact	10.0A
Voltage - Maximum	600V

Material Info

Engineering Number	SY16-3
--------------------	--------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130128 Series](#)