

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301370124](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, Cord Clamp, with Cover Plates for (2) Single 20/30A Locking Receptacles

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E46237

**General**

Product Family Power Distribution  
 Series [130137](#)  
 Enclosure Rating NEMA 4  
 GFCI Reset Manual  
 Mounting Style Portable  
 Open Neutral Relay N/A  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name Super-Safeway  
 Receptacle Type Single  
 Taxonomy Power Distribution  
 Type Multiple Outlet Box  
 UPC 78678875052

**Physical**

Cord Diameter 8.26-16.64mm (.325-.655")  
 Cord Grip Body Size N/A  
 Cord Length N/A  
 Feed-Thru No  
 Flip Lid No  
 Material - Housing Rubber  
 Number of Receptacles 1 - Customer Supplied  
 Packaging Type Carton

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact Per Cust. Supplied Receptacle  
 GFCI Yes  
 Ground Continuity Monitor No  
 NEMA Configuration NEMA L5-20  
 Voltage - Maximum Per Cust. Supplied Receptacle

**Material Info**

Engineering Number 3003



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130137 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**