

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301370127](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Super-Safeway Multiple Outlet Box, Standard Depth, 2-Sided, F2 (1/2"), NEMA 5-15 Duplex Receptacles with Flip Lids

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E46237

General

Product Family Power Distribution
 Series [130137](#)
 Enclosure Rating NEMA 4
 GFCI Reset N/A
 Mounting Style Portable
 Open Neutral Relay N/A
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Super-Safeway
 Receptacle Type Duplex
 Taxonomy Power Distribution
 Type Multiple Outlet Box
 UPC 78678874153

Physical

Cord Diameter 7.92-15.88mm (.312-.625")
 Cord Grip Body Size F2 1/2"
 Cord Length N/A
 Feed-Thru No
 Flip Lid Yes
 Material - Housing Rubber
 Net Weight 716.675/g
 Number of Receptacles 2
 Packaging Type Carton

Electrical

Cord Type N/A
 Current - Maximum per Contact 15.0A
 GFCI No
 Ground Continuity Monitor No
 NEMA Configuration NEMA 5-15
 Voltage - Maximum 125V

Material Info

Engineering Number 3005-1



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Not Relevant

REACH SVHC

Not Relevant

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Relevant

Search Parts in this Series

[130137 Series](#)