

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301380024

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Super-Safeway Multiple Outlet Coverplate, 20/30A Locking



Series image - Reference only

Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Power Distribution
Series	130138
Enclosure Rating	NEMA 4
GFCI Reset	N/A
Mounting Style	Permanent
Open Neutral Relay	N/A
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Super-Safeway
Receptacle Type	Single
Taxonomy	Power Distribution
Type	Multiple Outlet Box
UPC	78678875071
Physical	
Cord Diameter	12.70-22.23mm (.500-.875")
Cord Grip Body Size	F4 1"
Cord Length	1.83m (6.0')
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Nylon
Net Weight	17.236/g
Number of Receptacles	0
Packaging Type	Carton
Electrical	
Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA L5-20
Voltage - Maximum	125V
Material Info	
Engineering Number	3055

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Relevant
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130138 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION