

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301380029](#)  
**Status:** **Active**  
**Overview:** Watertite Extreme Wet-Location Wiring Solutions  
**Description:** Super-Safeway Multiple Outlet Coverplate, 20/30A Locking, Flip Lid

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Power Distribution
Series	<a href="#">130138</a>
Enclosure Rating	NEMA 4
GFCI Reset	N/A
Mounting Style	Permanent
Open Neutral Relay	N/A
Overview	<u>Watertite Extreme Wet-Location Wiring Solutions</u>
Product Name	Super-Safeway
Receptacle Type	Single
Taxonomy	Power Distribution
Type	Multiple Outlet Box
UPC	78678875074

**Physical**

Cord Diameter	12.70-22.23mm (.500-.875")
Cord Grip Body Size	F4 1"
Cord Length	N/A
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Nylon
Number of Receptacles	0
Packaging Type	Carton

**Electrical**

Cord Type	N/A
Current - Maximum per Contact	20.0A
GFCI	No
Ground Continuity Monitor	No
NEMA Configuration	NEMA L5-20
Voltage - Maximum	125V

**Material Info**

Engineering Number	3058
--------------------	------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130138 Series](#)