

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301430169](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Cordset 16 Gauge SOOW with Lock Blade, 3 Pole/3 Wire, Cordset Length 7.62m (25.0'), Non-NEMA, 15A/125V, 10A/250V

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E38085

**General**

Product Family [Wiring Devices](#)  
 Series [130143](#)  
 IP Rating N/A  
 NEMA Configuration [Non-NEMA Locking](#)  
 Overview [Heavy-Duty Industrial Wiring Devices](#)  
 Product Name Super-Safeway  
 Receptacle Type Single  
 Specialty N/A  
 Taxonomy [Wiring Devices](#)  
 Type Cordset  
 UPC 78678879561

**Physical**

Flange No  
 Flip Lid No  
 Gender Male-Female  
 Length 7.62m (25.0')  
 Locking Blade Yes  
 Net Weight 444.000/kg  
 Poles 3-pole/3-wire

**Electrical**

Cord Type 14/3 SOOW  
 Current - Maximum per Contact 10.0A, 15.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 125V / 250V

**Material Info**

Engineering Number 2407A143



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130143 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**