

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430189

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset 16 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 7.62m (25.0'), NEMA L5-15, 125V

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

Agency Certification

CSA

LR6837

UL

E38085

General

Product Family

Wiring Devices

Series

130143

IP Rating

IP67

NEMA Configuration

NEMA L5-15

Overview

Watertite Extreme Wet-Location Wiring Solutions

Product Name

Watertite Extreme

Receptacle Type

Single

Specialty

N/A

Taxonomy

Wiring Devices

Type

Cordset

UPC

78678879689

Physical

Cord Grip Body Size

F2 1/2"

Flange

No

Flip Lid

No

Gender

Male-Female

Length

7.62m (25.0')

Locking Blade

Yes

Net Weight

126.000/kg

Poles

2-pole/3-wire

Electrical

Cord Type

12/3 SOOW

Current - Maximum per Contact

15.0A

GFCI

No

Lighted Connector

No

Voltage - Maximum

125V

Material Info

Engineering Number

24W47A163

Reference - Drawing Numbers

Sales Drawing

1301430187-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

|                 |              |
|-----------------|--------------|
| China ROHS      | Not Reviewed |
| ELV             | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

China RoHS

Search Parts in this Series

130143 Series