

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430191

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Cordset 14 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 15.24m (50.0'), NEMA L5-15, 125V

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

Agency Certification

CSA

LR6837

UL

E38085

General

Product Family

Wiring Devices

Series

130143

IP Rating

IP67

NEMA Configuration

NEMA L5-15

Overview

Watertite Extreme Wet-Location Wiring Solutions

Product Name

Watertite Extreme

Receptacle Type

Single

Specialty

N/A

Taxonomy

Wiring Devices

Type

Cordset

UPC

78678879686

Physical

Cord Grip Body Size

F2 1/2"

Flange

No

Flip Lid

No

Gender

Male-Female

Length

15.24m (50.0')

Locking Blade

Yes

Net Weight

265.000/g

Poles

2-pole/3-wire

Electrical

Cord Type

12/3 SOOW

Current - Maximum per Contact

15.0A

GFCI

No

Lighted Connector

No

Voltage - Maximum

125V

Material Info

Engineering Number

24W47B143

Reference - Drawing Numbers

Sales Drawing

1301430187-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION