

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301430228](#)

**Status:** **Active**

**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)

**Description:** Watertite Extreme Standard Molded W Cordset, 2 Pole/3 Wire SOW Cordset, Cordset Length 0.91m (3.0') (3.0'), NEMA L5-20, 125V,Inline GFCI

**Documents:**

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
UL E38085

**General**

Product Family Wiring Devices  
Series [130143](#)  
IP Rating IP67  
NEMA Configuration NEMA L5-20  
Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
Product Name Watertite Extreme  
Receptacle Type N/A  
Specialty N/A  
Taxonomy Wiring Devices  
Type Cordset  
UPC 78678871301

**Physical**

Cord Grip Body Size F3 3/4"  
Flange No  
Flip Lid No  
Gender Male-Female  
Length 0.91m (3.0')  
Locking Blade Yes  
Net Weight 111.000/g  
Poles 2-pole/3-wire

**Electrical**

Cord Type 12/3 SJOW  
Current - Maximum per Contact 20.0A  
GFCI Yes-In-line  
Lighted Connector No  
Voltage - Maximum 125V

**Material Info**

Engineering Number 26W47E123IN



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130143 Series](#)