

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430252

Status:

Active

Overview:

Heavy-Duty Industrial Wiring Devices

Description:

Super-Safeway Cordset, 12 Gauge SOOW, 2 Pole/3 Wire, Cordset, Length 7.62m (25.0'), NEMA L5-30, 125V



Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

|                               |  |                                      |
|-------------------------------|--|--------------------------------------|
| Agency Certification          |  |                                      |
| CSA                           |  | LR6837                               |
| UL                            |  | E38085                               |
| General                       |  |                                      |
| Product Family                |  | Wiring Devices                       |
| Series                        |  | 130143                               |
| IP Rating                     |  | N/A                                  |
| NEMA Configuration            |  | NEMA L5-30                           |
| Overview                      |  | Heavy-Duty Industrial Wiring Devices |
| Product Name                  |  | Super-Safeway                        |
| Receptacle Type               |  | Single                               |
| Specialty                     |  | N/A                                  |
| Taxonomy                      |  | Wiring Devices                       |
| Type                          |  | Cordset                              |
| UPC                           |  | 78678870567                          |
| Physical                      |  |                                      |
| Flange                        |  | No                                   |
| Flip Lid                      |  | No                                   |
| Gender                        |  | Male-Female                          |
| Length                        |  | 7.62m (25.0')                        |
| Locking Blade                 |  | Yes                                  |
| Net Weight                    |  | 266.000/kg                           |
| Poles                         |  | 2-pole/3-wire                        |
| Electrical                    |  |                                      |
| Cord Type                     |  | 12/3 SOOW                            |
| Current - Maximum per Contact |  | 30.0A                                |
| GFCI                          |  | No                                   |
| Lighted Connector             |  | No                                   |
| Voltage - Maximum             |  | 125V                                 |
| Material Info                 |  |                                      |
| Engineering Number            |  | 2847A123                             |

|                                                               |              |
|---------------------------------------------------------------|--------------|
| EU ELV                                                        |              |
| Not Relevant                                                  |              |
| EU RoHS                                                       | China RoHS   |
| Not Relevant                                                  |              |
| REACH SVHC                                                    |              |
| Not Relevant                                                  |              |
| Halogen-Free                                                  |              |
| Status                                                        |              |
| Not Relevant                                                  |              |
| For more information, please visit <a href="#">Contact US</a> |              |
| China ROHS                                                    | Not Relevant |
| ELV                                                           | Not Relevant |
| RoHS Phthalates                                               | Not Relevant |

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION