

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301430273](#)
Status: **Active**
Overview: [Watertite Extreme Wet-Location Wiring Solutions](#)
Description: Watertite Extreme Cordset, 10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 30.48m (100.0'), NEMA L14-30, 125V/250V

Documents:

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR6837
 UL E38085

General

Product Family Wiring Devices
 Series [130143](#)
 Comments 125V and 250V
 IP Rating IP67
 NEMA Configuration NEMA L14-30
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)
 Product Name Watertite Extreme
 Receptacle Type N/A
 Specialty N/A
 Taxonomy Wiring Devices
 Type Cordset
 UPC 78678871089

Physical

Cord Grip Body Size F4 1"
 Flange No
 Flip Lid No
 Gender Male-Female
 Length 30.48m (100.0')
 Locking Blade Yes
 Net Weight 777.000/kg
 Poles 3-pole/4-wire

Electrical

Cord Type 12/3 SOOW
 Current - Maximum per Contact 30.0A
 GFCI No
 Lighted Connector No
 Voltage - Maximum 125V / 250V

Material Info

Engineering Number 28W74D104



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[130143 Series](#)