

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301430274](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** Watertite Extreme Cordset, 10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 7.62m (25.0'), NEMA L15-30, 3ø 250V

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E38085

**General**

Product Family Wiring Devices  
 Series [130143](#)  
 IP Rating IP67  
 NEMA Configuration NEMA L15-30  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name Watertite Extreme  
 Receptacle Type N/A  
 Specialty N/A  
 Taxonomy Wiring Devices  
 Type Cordset  
 UPC 78678871091

**Physical**

Cord Grip Body Size F4 1"  
 Flange No  
 Flip Lid No  
 Gender Male-Female  
 Length 7.62m (25.0')  
 Locking Blade Yes  
 Net Weight 541.000/kg  
 Poles 3-pole/4-wire

**Electrical**

Cord Type 12/3 SOOW  
 Current - Maximum per Contact 30.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 3ø 250V

**Material Info**

Engineering Number 28W75A104



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130143 Series](#)