

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301430277

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Cordset, 10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 7.62m (25.0'), NEMA L15-30, 3Ø 250V



Series image - Reference only

Documents:

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E38085
General	
Product Family	Wiring Devices
Series	130143
IP Rating	IP67
NEMA Configuration	NEMA L15-30
Overview	Watertite Extreme Wet-Location Wiring Solutions
Product Name	Watertite
Receptacle Type	N/A
Specialty	N/A
Taxonomy	Wiring Devices
Type	Cordset
UPC	78678871095
Physical	
Cord Grip Body Size	F4 1"
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Locking Blade	Yes
Net Weight	877.000/kg
Poles	3-pole/4-wire
Electrical	
Cord Type	12/3 SOOW
Current - Maximum per Contact	30.0A
GFCI	No
Lighted Connector	No
Voltage - Maximum	3Ø 250V
Material Info	
Engineering Number	28W75D104

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130143 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION