

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301460016](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** Watertite Extreme Cordset 16 Gauge SOOW, 3 Pole/3 Wire, Cordset Length 7.62m (25.0'), Non-NEMA 15A/125V, 10A/250V

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E38085

**General**

Product Family Wiring Devices  
 Series [130146](#)  
 IP Rating IP67  
 NEMA Configuration Non-NEMA  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name Watertite Extreme  
 Receptacle Type Single  
 Specialty N/A  
 Taxonomy Wiring Devices  
 Type Cordset  
 UPC 78678898069

**Physical**

Cord Grip Body Size F2 1/2"  
 Flange No  
 Flip Lid No  
 Gender Male-Female  
 Length 7.62m (25.0')  
 Locking Blade No  
 Net Weight 0.752/kg  
 Poles 3-pole/3-wire

**Electrical**

Cord Type 16/3 SOOW  
 Current - Maximum per Contact 15.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 250V

**Material Info**

Engineering Number 14W07A163

**Reference - Drawing Numbers**

Sales Drawing 1301460016-000



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130146 Series](#)