

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301470054

Status:

Active

Overview:

Watertite Extreme Wet-Location Wiring Solutions

Description:

Watertite Extreme Extra Hard Outdoor Connector With Locking Blade, 3 Pole/4 Wire, NEMA L14-20, 250V, Cord Grip Body Size F3, Black

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Brochure (PDF)

Agency Certification

CSA

LR6837

UL

E10176

General

Product Family

Wiring Devices

Series

130147

IP Rating

IP67

NEMA Configuration

NEMA L14-20

Overview

Watertite Extreme Wet-Location Wiring Solutions

Product Name

Watertite Extreme

Receptacle Type

Single

Specialty

N/A

Taxonomy

Wiring Devices

Type

Connector

UPC

78678871371

Physical

Cord Grip Body Size

F3 3/4"

Flange

No

Flip Lid

No

Gender

Female

Length

N/A

Locking Blade

Yes

Poles

3-pole/4-wire

Electrical

Cord Type

N/A

Current - Maximum per Contact

20.0A

GFCI

No

Lighted Connector

No

Voltage - Maximum

250V

Material Info

Engineering Number

27W74BLK

Reference - Drawing Numbers

Sales Drawing

1301470053-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

130147 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION