

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301470096](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** [Watertite Extreme Connector with Locking Blade, 2 Pole/3 Wire, NEMA L6-30, 125V, Cord Grip Body Size F4](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Brochure \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E10176

**General**

Product Family [Wiring Devices](#)  
 Series [130147](#)  
 IP Rating [IP67](#)  
 NEMA Configuration [NEMA L6-30](#)  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name [Watertite Extreme](#)  
 Receptacle Type [Single](#)  
 Specialty [N/A](#)  
 Taxonomy [Wiring Devices](#)  
 Type [Connector](#)  
 UPC [78678871332](#)

**Physical**

Cord Grip Body Size [F4 1"](#)  
 Flange [No](#)  
 Flip Lid [No](#)  
 Gender [Female](#)  
 Length [N/A](#)  
 Locking Blade [Yes](#)  
 Net Weight [439.980/g](#)  
 Poles [2-pole/3-wire](#)

**Electrical**

Cord Type [N/A](#)  
 Current - Maximum per Contact [30.0A](#)  
 GFCI [No](#)  
 Lighted Connector [No](#)  
 Voltage - Maximum [250V](#)

**Material Info**

Engineering Number [29W48](#)

**Reference - Drawing Numbers**

Sales Drawing [1301470096-000](#)



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130147 Series](#)