

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301500116](#)  
**Status:** **Active**  
**Overview:** [Watertite Extreme Wet-Location Wiring Solutions](#)  
**Description:** 100 Amp Watertite Pin and Sleeve Receptacle with Flip Lid, 3 Pole/4 Wire, 250V, Orange

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

UL E145923

**General**

Product Family Wiring Devices  
 Series [130150](#)  
 Comments IEC Configuration 309-1/309-2  
 IP Rating IP67  
 NEMA Configuration N/A  
 Overview [Watertite Extreme Wet-Location Wiring Solutions](#)  
 Product Name Watertite  
 Receptacle Type Single  
 Specialty Pin and Sleeve  
 Taxonomy Wiring Devices  
 Type Receptacle  
 UPC 78678870971

**Physical**

Flange Yes  
 Flip Lid Yes  
 Gender Female  
 Length N/A  
 Locking Blade Yes  
 Poles 3-pole/4-wire

**Electrical**

Cord Type N/A  
 Current - Maximum per Contact 100.0A  
 GFCI No  
 Lighted Connector No  
 Voltage - Maximum 250V

**Material Info**

Engineering Number 4100R12W

**Reference - Drawing Numbers**

Sales Drawing 1301500148-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130150 Series](#)