

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1301510012](#)  
**Status:** **Active**  
**Overview:** [Heavy-Duty Industrial Wiring Devices](#)  
**Description:** Super-Safeway Adapter NEMA 5-15 Receptacle - Female End 15A/125V, Non-NEMA Plug - Male End, 15A/125V

**Documents:**

[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                    |  |
|--------------------|--|
| Product Family     | Wiring Devices                                       |
| Series             | <a href="#">130151</a>                               |
| IP Rating          | N/A  |
| NEMA Configuration | NEMA 5-15  |
| Overview           | <a href="#">Heavy-Duty Industrial Wiring Devices</a> |
| Product Name       | Super-Safeway  |
| Receptacle Type    | N/A  |
| Specialty          | N/A  |
| Taxonomy           | Wiring Devices                                       |
| Type               | Adapter  |
| UPC                | 78678875002  |

**Physical**

|               |               |
|---------------|---------------|
| Flange        | No            |
| Flip Lid      | No            |
| Gender        | Male-Female   |
| Length        | N/A           |
| Locking Blade | No            |
| Poles         | 2-pole/3-wire |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Cord Type                     | N/A   |
| Current - Maximum per Contact | 15.0A |
| GFCI                          | No    |
| Lighted Connector             | No    |
| Voltage - Maximum             | 125V  |

**Material Info**

|                    |      |
|--------------------|------|
| Engineering Number | 1702 |
|--------------------|------|



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**China RoHS**

**Search Parts in this Series**

[130151](#) Series